



**MAINTENANCE  
INFORMATION**

**MI13-33**

DATE :	APRIL 2013	SECTION :	05 Colling System
SUBJECT :	NEW SILICONE HOSES AND HOSE CLAMPS		

***IMPORTANT NOTICE***  
*This modification is recommended by PrevoSt to increase your vehicle's performance. Note that no reimbursement will be awarded for carrying out this modification.*

**APPLICATION**

Upon replacement of :

- Generic polyester reinforced silicone hoses (sold by length).
- Generic 90deg polyester reinforced silicone elbows.
- 5/8po, 3/4po, 7/8po, 1 1/8po and 1 3/8po. constant torque hose clamps.

**DESCRIPTION**

Replacement of polyester reinforced silicone hoses and elbows by aramid reinforced hoses and elbows for improved long term durability.

Constant torque hose clamps for silicone hoses with 5/8po, 3/4po, 7/8po, 1 1/8po and 1 3/8po inside diameter (I.D) can be replaced by new WAVE SEAL type constant torque hose clamps. These new hose clamps allow for a higher tightening torque value (65 to 75 lb/in) and better keep their clamping force after installation.

**HOSE CLAMPS cross-reference :**

OLD PART #	DESCRIPTION	NEW PART #	DESCRIPTION
<b>504646</b>	HOSE CLAMP CT5 PS SS SL 13/16 - 1 5/16po	<b>504781</b>	HOSE CLAMP CT WS SS SL 13/16 - 1 5/16po
<b>504657</b>	HOSE CLAMP CT5 PS SS 1 11/32 - 2 1/16po	<b>504783</b>	HOSE CLAMP CT WS SS SL 1 11/32 - 2 1/16po
<b>504658</b>	HOSE CLAMP CT5 PS SS SL 1 3/16 - 1 5/16po	<b>504782</b>	HOSE CLAMP CT WS SS SL 1 3/16 - 1 5/16po

## SILICONE HOSES cross-reference :

OLD PART #	DESCRIPTION	NEW PART #	DESCRIPTION
<b>53643</b>	SILICONE ELBOW	<b>503804</b>	SILICONE ELBOW 90 DEG
<b>53644</b>	SILICONE ELBOW	<b>503805</b>	SILICONE ELBOW 90 DEG
<b>372131</b>	ELBOW REDUCER 90 DEG	<b>503794</b>	SILICONE ELBOW 90 DEG.
<b>373829</b>	SILICONE HOSE 1 1/8 1160MM	<b>503796</b>	SILICONE HOSE 1 1/8" X 6'
<b>374377</b>	SILICONE ELBOW	<b>374616</b>	SILICONE ELBOW
<b>503395</b>	SILICONE HOSE 2 3/4x3'	<b>503787</b>	SILICONE HOSE 2 3/4" X 6'
<b>503684</b>	SILICONE HOSE 7/8x100'	<b>503803</b>	SILICONE HOSE 7/8" X 100'
<b>503720</b>	SILICONE HOSE 5/8X100'	<b>503802</b>	SILICONE HOSE 5/8" X 100'
<b>503722</b>	SILICONE HOSE 2 1/2" X 4'	<b>503786</b>	SILICONE HOSE 2 1/2" X 6'
<b>503758</b>	SILICONE HOSE 2 3/8" x 4 Pl.	<b>503785</b>	SILICONE HOSE 2 3/8" X 6'
<b>503774</b>	SILICONE HOSE 2 1/4" X 48"	<b>503801</b>	SILICONE HOSE 2 1/4" X 6'
<b>503779</b>	SILICONE HOSE 3/8 ID	<b>503806</b>	SILICONE HOSE 3/8" X 100'
<b>503790</b>	SILICONE HOSE 3/8" X 25' E	<b>503806</b>	SILICONE HOSE 3/8" X 100'
<b>503791</b>	SILICONE HOSE 7/8 ID X 4'	<b>503797</b>	SILICONE HOSE 7/8" X 6'
<b>572049</b>	SILICONE HOSE 2" ID	<b>503784</b>	SILICONE HOSE 2" X 12'
<b>871031</b>	SILICONE ELBOW FLEXIBLE 90 DEG	<b>503794</b>	SILICONE ELBOW 90 DEG.
<b>871099</b>	SILICONE HOSE REDUCER 1 1/2" I.D. X 1 3/8" I.D.	<b>503798</b>	SILICONE HOSE REDUCER 1 1/2" I.D. X 1 3/8" I.D.
<b>70396483</b>	SILICONE HOSE	<b>053617</b>	SILICONE HOSE 105 +/- 12 LG

**NOTE**

Material can be obtained through regular channels.

**Waste disposal:**

Discard according to applicable environmental regulations (Municipal/State[Prov.]/ Federal)

Access all our Service Bulletins on  
<http://prevostparts.volvo.com/technicalpublicatios/en/pub.asp>  
 Or scan the QR-Code with your smart phone.

E-mail us at [technicalpublications\\_prev@volvo.com](mailto:technicalpublications_prev@volvo.com) and type "ADD" in the subject to receive our warranty bulletins by e-mail

